

4. Double filter

Usage: The double filter are used to filter fresh milk, sugar fluid, drink, liquid cement, Chinese medicine fluid etc to remove each kind of slight pellet impurity in liquid accurately. The two filtering drums can work simultaneously or carry on the filtration in turn, changing filtering net without turning off the machine, especially suitable in the continuous production. It has advantages like filtering quick, low cost, easy operation etc.

Main parameters:

Model	: ZHP-1
Quantity	: 1 piece
Overall size	: 250*800*1200mm
Framework material	: SUS304



5. High pressure homogenizer

Usage: The GJB stretch high pressure homogenizer is a widely used device for homogenization of liquid and materials. It is widely used in the fields of dairy product, drinks, edible chemical medicine and biological technology. The material and liquid is homogenized under high pressure so as to reduce the delamination and increase the pureness, looseness of the material and liquid to improve the quality of mixture.

Main parameters:

Model	: GJB25-0.5
Rated pressure	: 25 Mpa
Rated flow	: 0.5 m ³ /h
Suitable material	: liquid such as milk, soy milk, oil
Material temperature	: ≤85℃
Pipe diameter of inlet orifice	: φ25mm
Pipe diameter of discharge hole	: φ15mm
Motor power	: 4kw
Overall size L*W*H	: 800*480*1000mm
Weight	: 500kg



8. Vacuum degasser

Usage: the vacuum degasser is an indispensable piece of equipment in the production line of juice and tea. It is mainly used for the desecration of homogenized juice in vacuum so as to avoid the oxidation to prolong its preservation.

Main parameters:

Model	: TQ-500
Quantity	: 1 piece
Treatment capacity	: 500 kg/h
Framework material	: stainless steel



Note :
Due to keeping innovation,
the specification and
Machine pictures or color
are subject to alteration
without notice!