



9. Semi-auto ultra-temperature instantaneous sterilizer

Usage: The ultra-temperature instantaneous sterilizer is used to sterilize the juice by instantaneous super-temperature heating. The temperature will reach between 115°C and 135°C, so the effect of sterilization is very good. And the time of sterilization is very short so that the product keeps high quality. It is widely used in the production of fresh milk, soybean milk, juice, beverage, and so on.

Main parameters:

Quantity : 1 piece
Capacity : 500kg per hour
Framework material : Stainless steel 304



10. Insulation tank

Main parameters:

Quantity : 1 piece
Volume for one tank : 500L
Framework material : SS304



Filling And Packing System

1. Washing machine

Usage: the washing machine is used for washing the can used before filling. The water is treated by water treatment system.

Main parameter:

- 1) Quantity: 1 set
- 2) Model: XG-2
- 3) Capacity: 2000 bottle per hour
- 4) Power: 0.55kw
- 5) Overall size: 1050*400*1600
- 6) Material: SUS304

Note :

Due to keeping innovation,
the specification and
Machine pictures or color
are subject to alteration
without notice!

