

OPTIONAL ACCESSORIES

1. Auto CIP cleaning system



Usage: the CIP equipment is used to clean material pipes and containers at site in trades, such as milk products, juice, beverage and etc. a centrifugal pump is used in CIP to convey cleansing liquid into material pipe and equipment to force the cleansing liquid to circulate to make cleaning without taking apart pipes or equipment. Using the system, the equipment availability can be improved and intensity of labor lessened.

Main parameters:

Working pressure	: normal pressure in tank, 0.3-0.7Mpa in steam pipe
Working temperature	: 60-138°C in acid and alkaline tank, water tank, steam pipe
Material name	: acid and alkaline liquid tank, 1% nitric acid, 1% caustic soda liquid Steam pipe, steam
Centrifugal pump	: 15 ton per hour
Maximal centrifugal pressure head	: 24m
Motor power	: 4 kW
Overall size	: 3500*1800*2200mm
Weight	: 2.5 ton

Note :

Due to keeping innovation,
the specification and
Machine pictures or color
are subject to alteration
without notice!