

RJWJ-150A

RJWJ-150A soft capsule produce equipment

RJWJ-150A-type soft capsule host PLC to control the use of technology and the use of pneumatic compression of the mold roll, thereby extending the tool life, it is stable, easy to operate, well-equipped, well-produced set of equipment, and materials research, in full compliance with GMP requirements, widely used in the pharmaceutical industry, cosmetics, health products, pesticides and other industries.



Note :

Due to keeping innovation, the specification and Machine pictures or color are subject to alteration without notice!

RJWJ-150A technique parameter

Rolling Mold Speed	0-6 rpm/min
Rolling Mold Size	102x152mm
Loaded the Volume Difference	±2%
Motor Power	1.1kw
Over Dimension	750x950x1910(h)mm
Weight	850kg

RJWJ-150A mainly advantage

- Newly developed frequency-conversion control air-cooling set, which avoids instability of capsule press parameter.
- The gelatin is carried by gelatin tank through horizon gelatin conveyor, which improves working environment.
- Gelatin conveyor is stainless steel conveyor, the humanized design makes operation convenient.
- The tumbler drier is also stainless steel made, no dead angle in cog rolling, easily to clean.
- There is a basin below the tumbler, so no oil stain stays.
- The clearance between two dies is pneumatically adjusted, naturally prolonged the life of the rolling die.
- All the electrical components are imported famous brand products, with stable performance.
- Those parts contacting capsule are 304 or 316L fine stainless steel manufactured except injection segment, spreader box, rolling die, and in strict accordance with GMP standards.