



RJWJ-PY

RJWJ-PY stirred with liquid equipment

This series of open-pot is stirred with liquid capsules of the production process of liquid ingredients, such as sedimentation and mixing processes in the equipment, with a folder dwelling size, insulation type.



Note :

Due to keeping innovation, the specification and Machine pictures or color are subject to alteration without notice!

RJWJ-PY technique parameter

Refrigeration device	by two compressors
Stirring motor	6 W, 1200 RPM
Temp. range	ambient temperature - -70°C
Temp. controlling accuracy	$\pm 0.1^{\circ}\text{C}$
Constant temp. bath	5,8 L with stainless steel innar tank
Temp. sensor	Industrial platinum, Pt 100
Total power consumption	not more than 1700 W